





Achtung: The result of the rolling process has to be checked on the basis of the reference dimensions in this roller plan. Please note the examination advices of the current roller manual
Attention:



		Stck. Qty.	Art.-Nr. Art.-No. für Isomat 3/5	Art.-Nr. Art.-No. für Isomat 4	Bestückungsfolge (v. innen nach außen) Assembly sequence (inside to outside)			Stck. Qty.	Art.-Nr. Zubehör Art.-No. Accessories
		R1	6	282821	(20.0 mm)				
A1		1	282590 B	282590 B	R1/A1				
A2		1	282590 B	282590 B	R1/A2				
A3		1	282591 B	282590 B	R1/A3				
A4		1	282591 B	282590 B	R1/A4				
F1		1	282592 B		R1/F1				
F2		1	282592 B		R1/F2				
		Zulässige Abweichung Permissible tolerance		Oberflächenabwicklung Circumference		VP PU		Info-Plan:	
				mech. polished uml. total		Maßstab Scale		Gewicht Weight	
		Paßmaße Close tol.				1 : 1			
		Abmaße Std. tolerance				Werkstoff Material			
Original / Änderung Revision / Version		0100		Datum Date		Name		Benennung Title	
				19.12.2018				Roller plan Isomat 3/4/5	
								Schüco AWS 75.SI	
								IsoModul	
								519177 RP 1000	